


WAVELENGTH STABILIZED 1064 nm / 1030 nm HIGH POWER MINI-BUTTERFLY DFB LASER DIODE MODULE

CMDFB1064A

CMDFB1030A

The Coherent CMDFB10xxA wavelength stabilized high power single mode laser module has been designed as a light source for pulsed narrow bandwidth fiber laser and direct frequency conversion applications. A distributed feedback grating (DFB) located in the laser cavity results in the wavelength stabilization within couple of round trips. The laser chip and package are optimized for subnanosecond pulse operation. Processes and techniques of coupling the fiber to the laser allow high peak output powers that are very stable with both time and temperature.



FEATURES

- Wavelengths : 1064 or 1030 nm
- High output CW and pulse power: 200 and 800 mW, respectively
- Short pulse modulation, down to 100 ps
- Lateral and longitudinal single mode in short pulse operation
- Polarization maintaining single mode optical fiber
- Internal thermoelectric heat pump and monitor diode
- Hermetically sealed 10-pin mini-butterfly package
- High reliability

APPLICATIONS

- Fiber laser systems
- Frequency conversion
- Spectroscopy

WAVELENGTH STABILIZED 1064 nm / 1030 nm HIGH POWER MINI-BUTTERFLY DFB LASER DIODE MODULE

Optical Characteristics

Case temperature -20 to +75°C Submount temperature 25°C

Parameter	Min	Typ	Max	Unit	Conditions
Threshold current	15	40	70	mA	
Peak wavelength					
CMDFB1064A	1061.5	1063.5	1065.5	nm	
CMDFB1030A	1028	1030	1032	nm	
Operating CW current			400	mA	Also for current pulses >200 ns
CW output power	150	200		mW	
Forward voltage		2	2.5	V	

Pulse modulation:

Optical pulse width	10		200	ns	
Operating pulsed peak current			0.8	A	
Pulsed peak power	300	400		mW	
Duty cycle			5	%	

Short pulse modulation:

Optical pulse width	~0.1		10	ns	~100 ps is achievable in gain switching regime with dedicated pulse driver
Operating pulsed peak current			1.6	A	
Pulsed peak power	600	800		mW	
SMSR	20			dB	Tested and guaranteed only at 1.5ns pulse width, 300 kHz repetition rate, no bias
Duty cycle			1	%	
Chip series resistance		2		Ohm	Small signal equivalent circuit parameters for laser chip
Chip capacitance		50		pF	

Absolute Maximum Ratings


Parameter	Min	Max	Unit
Storage temperature	-40	85	°C
CW laser forward current (10 s max)		1.5	A
Laser reverse voltage		2	V
Heat pump current	-2.2	2.2	A
Heat pump voltage	-3.3	3.3	V
Lead soldering temperature (10 s max)		350	°C
Fiber bend radius	20		mm

WAVELENGTH STABILIZED 1064 nm / 1030 nm HIGH POWER MINI-BUTTERFLY DFB LASER DIODE MODULE

Fiber Characteristics

Parameter	Min	Typ	Max	Unit
Fiber type: Polarization maintaining Nufern PM980-HP or equivalent (e.g. Fujikura SM98)				
Mode field diameter	5.6	6.6	7.6	μm
Buffer diameter	230	250	270	μm
Fiber length (module case to fiber end)	1			m
Pristine fiber proof test level	200			psi
Fiber pull to housing	150			psi

Connections



Pin	Description	Pin	Description
1	TEC (+)	6	Laser anode (+)
2	Thermistor	7	Laser cathode (-)
3	Monitor anode (-)	8	NC
4	Monitor cathode (+)	9	Package ground
5	Thermistor	10	TEC (-)

RoHS Compliance

Coherent is fully committed to environment protection and sustainable development and has set in place a comprehensive program for removing polluting and hazardous substances from all of its products. The relevant evidence of RoHS compliance is held as part of our controlled documentation for each of our compliant products. RoHS compliance parts are available to order, please refer to the ordering information section for further details.

Ordering Information

CMDFB1064A	1064 nm 10-pin miniBTF Module with DFB
CMDFB1030A	1030 nm 10-pin miniBTF Module with DFB

Important Notice

Performance figures, data and any illustrative material provided in this data sheet are typical and must be specifically confirmed in writing by Coherent before they become applicable to any particular order or contract. In accordance with the Coherent policy of continuous improvement specifications may change without notice. Further details are available from any Coherent sales representative.

Safety Labels



Caution - use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.