
MLU96ZW***-7*

The Coherent MLU96ZW-series uncooled pump laser module represents continuing innovation in packaging technology to enable highly reliable pump laser sources for existing and emerging applications.



FEATURES

- Ultra-small package footprint: 10x4.4x3.2 mm (LxWxH)
- Up to 400 mW operating power over full temperature range
- -20 to 85°C Extended operating temperature range
- Low power consumption
- Low bend-loss, 80 μm, PM fiber supporting 5 mm bend radius
- Wavelength stabilized by fiber Bragg grating over entire operating range
- Centre wavelength at 974 or 976 nm
- Telcordia GR-468-CORE compliant
- RoHS compliant

APPLICATIONS

- Integrated amplification within high bit-rate transceiver modules
- Low noise EDFA requiring higher optical power with low power consumption and small formfactor package
- Single or multi-stage EDFA applications including Singlechannel and DWDM designs



Housed within an ultra-compact 3-pin micro-format package with a volume of just 141 mm³, the laser module enables equivalent performance to the Coherent leading 8-pin uncooled mini-DIL products.

The MLU96ZW-series provides designers of ultra-compact integrated amplifier systems with the tools to enable low-noise, high power optical amplification within package volumes previously unachievable.

Combining a small package volume, 1mm fibre feedthrough, and low bend-loss 80 µm PM fibre, the module can enable integrated optical amplification within small form-factor platforms such as CFP2 and CFP4.

With <2 W maximum power consumption and supporting an extended -20 to 85°C operating temperature range, the MLU96ZW-series pump fits within tight power-consumption budgets and addresses uncontrolled environmental requirements.

The MLU96ZW-series houses the market-proven Coherent enhanced G08 laser for superior reliability and stability, and the package is qualified to the requirements of Telcordia GR-468-CORE.

Optical Characteristics

Product Code	Minimum Kink-Free Power	Maximum Operating Power	Typical Operating Current @85°C	Maximum Operating Current@85°C	Total power consump- tion @ Max operating conditions
	P _{kink} (mW)	P _{op} (mW)	l _{op} (mA)	I _{op} (mA)	(W)
MLU96ZW100-7*	110	100	260	340	0.49
MLU96ZW120-7*	135	120	308	397	0.58
MLU96ZW140-7*	155	140	348	453	0.65
MLU96ZW160-7*	175	160	382	505	0.75
MLU96ZW180-7*	200	180	432	561	0.84
MLU96ZW200-7*	220	200	474	618	0.95
MLU96ZW220-7*	245	220	517	675	1.06
MLU96ZW240-7*	265	240	561	747	1.19
MLU96ZW260-7*	285	260	605	803	1.33
MLU96ZW280-7*	310	280	646	865	1.43
MLU96ZW300-7*	330	300	689	927	1.54
MLU96ZW320-7*	350	320	732	989	1.65
MLU96ZW340-7*	375	340	774	1000	1.70
MLU96ZW360-7*	395	360	817	1000	1.80
MLU96ZW380-7*	420	380	860	1000	1.90
MLU96ZW400-7*	440	400	903	1000	2.00

Notes:



^{1.} Typical and maximum operating currents at 85°C

^{2.} Operating power assumes a 10% ageing margin: Operating Power = Kink Free Power / 1.1

Wavelength Specification

Product Code	Min.	Тур.	Max.	Units	Condition
MLU96Z***-74	972	974	976	nm	Air reference.
MLU96Z***-76	974	976	978		@ 0°C to 80°C case temperature.

Product Specification ¹

Parameter		Min.	Тур.	Max.	Units	Condition
Threshold Current	l _{th}		55	100	mA	
Operating Forward Voltage	V _{op}		1.65	2.0	V	
Spectral Width	Δλ		0.2	1.0	nm	RMS at -13 dB
Power in Band Ratio	PIB				%	λc ±1.5 nm, 0°C to 80°C
>100 mW		90				
50 mW to 100 mW		75				
Fiber Power Stability	ΔP ₋ t				dB	Peak-to-peak
>30 mW	·			0.10		Time = 60 sec
20 – 30 mW				0.10		DC to 50 kHz
10 – 20 mW				0.15		
5 – 10 mW				0.20		
Return Loss	RL	35			dB	1500 nm – 1600 nm

Note 1: All characteristics at <-40 dB back reflection

Absolute Maximum Ratings

Parameter		Min.	Тур.	Max.	Units	Condition
Operating Case Temperature	T	-20		85	°C	
Storage Temperature	T _{sta}	-40		85	°C	
Storage Relative Humidity	RH _{stg}	5		95	%	But not to exceed 0.024 kg of water per 1.0 kg of dry air
Operating Relative Humidity	RH	5		85	%	
Pigtail Axial Pull Force				0.25	kg	1 minute
Fiber Bend Radius		5			mm	
Lead Soldering Temperature				350	°C	10 sec
Laser Diode Forward Current	If max			1100	mA	
Laser Diode Current Transient				1200	mA	Time = 1000 ns max
Laser Diode Reverse Current				10	μΑ	
Laser Diode Reverse Voltage	V _r			2.0	V	
ESD Threshold				500	V	HBM, C = 100 pF, R = 1.5 kΩ




Fiber Specification

Parameter	Min.	Тур.	Max.	Units	Condition
Fiber Type					80 μm PM Fibre
Cut-off Wavelength	870		950	nm	
Mode Field Diameter		6.0		μm	@ 980 nm
Cladding Diameter	79	80	81	μm	
Fiber Coating Diameter	155	165	175	μm	Acrylate material, mechanically strippable
Core/cladding Concentricity			<0.5	μm	
Fiber Proof Test	200			kpsi	
Fibre Length	750			mm	No re-coated region along length

Notes:

Module Outline Drawing and Pin Connections





^{1.} Fiber termination; bare fiber with rough cleave.

Ordering Information

MLU	96Z	W	***		7*
Product Type	Chip Type	-20 to 85°C	LD Operating Power (mW)	-	Wavelength
		Temperature Range			74 for 974 nm
					76 for 976 nm

Example: MLU96ZW220-74 is a 220 mW Operating Power, 974 nm product

RoHS Compliance 50



Coherent is fully committed to environment protection and sustainable development and has set in place a comprehensive program for removing polluting and hazardous substances from all of its products. The relevant evidence of RoHS compliance is held as part of our controlled documentation for each of our compliant products. RoHS compliance parts are available to order, please refer to the ordering information section for further details.

User & Product Safety

Invisible laser radiation. Avoid eye or skin exposure to direct or scattered radiation. Class 4 laser product, ESD protection. Caution. Static sensitive device. To be opened by authorised personnel only.







Caution - use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

THIS PRODUCT COMPLIES WITH 21CFR 1040.10

Important Notice

Performance figures, data and any illustrative material provided in this data sheet are typical and must be specifically confirmed in writing by Coherent before they become applicable to any particular order or contract. In accordance with the Coherent policy of continuous improvement specifications may change without notice. Further details are available from any Coherent sales representative.

This product is protected by patents and patent applications pending worldwide.

