

Contacts:

Magnus Pålsson

Coherent, Inc.
+46 31 706 27 72

Magnus.Palsson@optoskand.se

David Kuntz

Technical Marketing Services
(310) 377-5393

davidkuntz@cox.net

For Immediate Release:

New Fiber to Fiber Coupler with Power Handling Capability of 12 kW (CW)

Santa Clara, CA USA, 06/26/2017 – A new Fiber to Fiber Coupler (FFC) from Coherent (formerly Optoskand AB) enables the use of replaceable, process fiber optic cables so that integral components of the fiber laser – most notably the feeding fiber – are not exposed to opto-mechanical damage, even in harsh industrial processes. Damage to the feeding fiber means long and often costly down time. But the new FFC enables the use of a separate fiber interface, and this separate delivery fiber can be exchanged in minutes in the case of damage.

The FFC is an eye-safe, stand-alone, water-cooled photonic component that handles laser power levels of 12 kW. A range of options enables coupling between fibers of different core diameters, as well as commonly used connector interfaces (QB, QD and Q5).

The FFC incorporates DGUV-certified safety electronics, and is an extension of the feeding fiber interlock circuit. It also includes integrated sensors, monitored and controlled by CANopen communication, whose threshold values can be set to enable or disable the interlock circuitry.

The FFC is ideal for high power industrial applications of fiber lasers, including Coherent HighLight FL series products.

###

Founded in 1966, Coherent, Inc. is one of the world's leading providers of lasers and laser-based technology for scientific, commercial and industrial customers. Our common stock is listed on the Nasdaq Global Select Market and is part of the Russell 2000 and Standard & Poor's MidCap 400 Index. For more information about Coherent, visit the company's website at www.coherent.com for product and financial updates.