
UM96Z***-7*

The high power, extended temperature UM96Z-series uncooled laser module in a 10-Pin mBTF package is Coherent's third-generation uncooled pump module providing higher powers and lower consumption.

This laser enables designers to create reliable SFF single- and multi-channel, high bit-rate, per-channel amplification as well as replace traditional cooled pumps in high power EDFA applications with reduced power consumption.



FEATURES

- Up to 500mW kink-free power over full operating temperature range
- Operating temperature range from -5°C to +75°C
- Polarization maintaining (PM) fiber
- Low power dissipation
- Small form factor mini-DIL package
- Wavelength stabilized by fiber Bragg grating over entire operating range
- Centre wavelength at 974 and 976nm
- Telcordia GR-468-CORE compliant
- RoHS compliant

APPLICATIONS

- Low noise EDFA requiring higher optical power with low power consumption and small form-factor package
- Single or multi-stage EDFA applications including Singlechannel and DWDM designs



The UM96Z-series uses a 10-pin mBTF package enabling smaller form factor designs, with mounting holes for ease of integration and thermal management. The 10-pin mBTF package is backward compatible with 14pin BTF package footprint and pinout.

The UM96Z-series is designed for uncooled operation at high temperature and power levels. Qualification of the enhanced G08 chip ensures high reliability even at 460mW operating power, 75°C. External Fiber Bragg Grating (FBG) stabilization provides excellent wavelength and power stability over the entire operating temperature range.

Optical Characteristics

Product Code	Minimum Kink-Free Power P _{kink} (mW)	Maximum Operating Power P _{op} (mW)	Typical Operating Current I _{op} (mA)	Maximum Operating Current I₀, (mA)
UM96Z280-7*	310	280	560	635
UM96Z290-7*	320	290	585	660
UM96Z300-7*	330	300	600	680
UM96Z310-7*	340	310	615	695
UM96Z320-7*	350	320	630	715
UM96Z330-7*	365	330	655	740
UM96Z340-7*	375	340	670	760
UM96Z350-7*	385	350	690	785
UM96Z360-7*	395	360	710	805
UM96Z370-7*	405	370	730	830
UM96Z380-7*	420	380	745	845
UM96Z390-7*	430	390	765	865
UM96Z400-7*	440	400	780	885
UM96Z410-7*	450	410	805	915
UM96Z420-7*	460	420	820	930
UM96Z430-7*	475	430	840	950
UM96Z440-7*	485	440	855	970
UM96Z450-7*	495	450	875	985
UM96Z460-7*	505	460	895	1000

Notes:

Wavelength Specification

Product Code		Min.	Тур.	Max.	Units	Condition
UM96Z***-74	λc	973	974	975	nm	Air reference.
UM96Z***-76		975	976	977	nm	FBG temperatures is @ 25°C.



^{1.} Typical and maximum operating currents at 75°C

^{2.} Operating power assumes a 10% ageing margin: Operating Power = Kink Free Power / 1.1

Product Specification

Parameter		Min.	Тур.	Max.	Units	Condition
Threshold Current	l _{th}		55	100	mA	
Operating Forward Voltage	V _{op}		1.85	2.0	V	
Spectral Width	Δλ		0.2	1.0	nm	RMS at -13 dB
Power in Band Ratio >100 mW 50 mW to 100 mW	PIB	90 75			%	λc ±1.5 nm, -5°C to 75°C
Temperature Dependence of Peak Wavelength	Δλ/Τ		0.008	0.01	nm/°C	FBG temperature dependency
Monitor Detector Responsivity	R _m	0.3	6	15	μA/mW	
Monitor Dark Current	dark			60	nA	-5V bias voltage
Fiber Power Stability >30 mW 20 – 30 mW 10 – 20 mW 5 – 10 mW	ΔP _f _t			0.10 0.10 0.15 0.20	dB	Peak-to-peak Time = 60 sec DC to 50 kHz
Return Loss	RL	35			dB	1500 nm – 1600 nm
Thermistor BETA Value	β	3500		4100		
Thermistor Resistance	R _{th}	9.5	10.0	10.5	kΩ	At submount temperature of 40°C
Heat Pump Power	P _{thermal}		1.35	1.75	W	Tcase = 75°C, 460 mW
Total Module Power Consumption	P _{Total}		1.8	2.2	W	

Notes:



^{1.} Conditions unless otherwise stated: Case temperature -5 to 75°C, Monitor diode bias -5V, CW operation

Absolute Maximum Ratings

Parameter		Min.	Тур.	Max.	Units	Condition
Operating Case Temperature	T _{op}	-5		75	°C	
Storage Temperature	T _{stg}	-40		85	°C	
Storage Relative Humidity	RH _{stg}	5		95	%	But not to exceed 0.024 kg of water per 1.0 kg of dry air
Operating Relative Humidity	RH _{op}	5		85	%	
Pigtail Axial Pull Force				0.5	kg	1 minute
Pigtail Side Pull Force				0.25	Kg	90°, 4 directions, 5 s
Fiber Bend Radius		13			mm	
Lead Soldering Temperature				350	°C	10 sec
Laser Diode Forward Current	If_ _{max}			1100	mA	CW
Laser Diode Current Transient				1200	mA	Time = 1000 ns max
Laser Diode Reverse Current	l _r			10	μΑ	
Laser Diode Reverse Voltage	Vr			2.0	V	
Photodiode reverse voltage				20	V	
Photodiode reverse current				5	mA	
ESD threshold				500	V	HBM, C = 100 pF, R = 1.5 kΩ


Fiber Specification


Parameter		Min.	Тур.	Max.	Units	Condition
Fiber Type	PM980					
Cut-off Wavelength		870	920	970	nm	
Mode Field Diameter		6.1	6.6	7.1	μm	@ 980nm
Cladding Diameter		124	125	126	μm	
Fiber Coating Diameter		230	245	255	μm	Acrylate material, mechanically strippable
Grating Recoat Diameter		260	290	320	μm	
Core/cladding Concentricity				≤0.3	μm	
Coating-clad Offset				≤5	μm	
Fiber Proof Test		200			kpsi	
Fiber Bragg Grating Proof Test		150			kpsi	


^{1.} Fiber termination: bare fiber with rough cleave



Module Outline Drawing and Pin Connections







Pin	Description	Pin	Description
1	NC	6	Laser anode (+)
2	Thermistor	7	Laser cathode (-)
3	Monitor anode (-)	8	NC
4	Monitor cathode (+)	9	Package ground
5	Thermistor	10	NC



Ordering Information

UM	96Z	***	-	7*
Product Type	Chip Type	LD Operating Power (mW)	-	Wavelength 74 for 974 nm 76 for 976 nm

Example: UM96Z310-74 is a 310mW Operating Power, 974nm product.

RoHs Compliance


Coherent is fully committed to environment protection and sustainable development and has set in place a comprehensive program for removing polluting and hazardous substances from all of its products. The relevant evidence of RoHS compliance is held as part of our controlled documentation for each of our compliant products. RoHS compliance parts are available to order, please refer to the ordering information section for further details.

User Safety











Caution - use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Important Notice

Performance figures, data and any illustrative material provided in this data sheet are typical and must be specifically confirmed in writing by Coherent before they become applicable to any particular order or contract. In accordance with the Coherent policy of continuous improvement specifications may change without notice. Further details are available from any Coherent sales representative.

